

Nylon Convenience Adapter, NEMA 5-15P
To NEMA 5-20R

By Hubbell Wiring Device-Kellems
Catalog # [HBL2270](#)

Nylon Convenience Adapter, NEMA 5-15P To NEMA 5-20R



Features

- Male Blade End
- Female Slot End

Application

Straight Blade to Straight Blade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL Listed
Nema Rating	5-15P to 5-20R

Conductor

Number Of Wires	3-Wire Grounding
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A
Phase	Single Phase
Current / Amperage Rating	15 A

Connectivity	Plug-In
Wattage	2500
Voltage Rating	125 VAC

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	White
Item Type	Plug-In Adapter
Material - Mounting Hardware	Plug-In
Material	Thermoplastic
Specifications	• Female End - 5-20R, 20A 125V • Male End - 5-15P, 15A 125V • Product Type - Nylon Convenience Adapters
UPC	783585809021

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)