

Locking Devices, Twist-Lock®, Industrial, Female Connector Body, 30A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non-Grounding, Non-NEMA

By Hubbell Wiring Device-Kellems
Catalog # [HBL3433C](#)



Twist-Lock® Industrial Female Connector Body 30A

Features

- Ribbed nylon housing provides a secure grip and impact and chemical resistance
- Superior cord grip design protects terminations from excess strain
- Clear, funnel shaped wire entry for ease of termination
- Integral dust shield protects wiring chamber from dust or contaminants

Application

Heavy Duty Industrial

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - HB or better per UL94 or CSA 22.2 No. 0.6, Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact), Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only., Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Nema Rating	Non-NEMA

Conductor

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG
Number Of Poles	4-Pole
Cable Range	0.350 - 1.150 in

Current

Dielectric Strength	Withstands 2,000V minimum
Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	3 Phase WYE 120/208 VAC
Phase	Three Phase

Current / Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Voltage Rating	3 Phase WYE 120/208 VAC

Dimensions

Display Size	Standard
Length	2.33 in
Width	2.33 in
Weight	0.40 lb.
Height	3.86 in
Dimensions	2.33 in x 2.33 in x 3.86 in

General

Cord Range	0.350"-1.150" (9-29)
Color	Black, White
Item Type	30A Non-Grounding Insulgrip® Connector
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted Connector Body
Type	Nylon
Material	
Specifications	<ul style="list-style-type: none"> • Assembly Screws - Steel - nickel plated • Contacts - Brass • Housing / Cord Clamp - Nylon • Terminal Clamp - Cold rolled steel - nickel plated • Terminal Retainer - Clear polycarbonate • Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)

UPC 783585039893

Logistics

Carton Quantity	30
Pallet Quantity	2880

Operational

Temperature Rating	<ul style="list-style-type: none"> • Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	---

Operating Temperature

Maximum continuous 75°C and
minimum -40°C without Impact

Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
WDK_MX-HBL3433C-SPEC-EN | REV 1/2026