

EdgeConnect™ Series, Locking Devices, Plug, Industrial/Commercial Grade, 2-Pole 3-Wire Grounding, 15A 250V, L6-15P, Black and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL4570CST](#)

EdgeConnect™, Locking Devices, Plug, Industrial/Commercial Grade, 2-Pole 3-Wire Grounding, 15A 250V, L6-15P, Black and White



Features

- Spring termination for a faster and more secure terminal connection
- Ribbed housing is impact and chemical resistant
- Superior cord grip design protects terminations from excess strain
- Accepts #14 - #10AWG, solid or stranded

Application

Extra Heavy Duty Industrial/Commercial Grade

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 V-2, Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact), Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Contact Manufacturer
Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified to C22.2 No. 42 File 280 • Fed. Spec. W-C596G • NEMA® WD-6 Compliant
Nema Rating	L6-15P

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Conductors	3-Wire Grounding
Conductor Range	#14 AWG to #10 AWG
Number Of Poles	2-Pole

Configuration

Cord Type

All Listed Portables

Current

Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Spring Termination
Voltage Rating	250 V

Dimensions

Display Size	Standard Sized Product
Size	1.32 in x 0.83 in x 3.28 in
Weight	0.2 lb.

General

Series	EdgeConnect™ Series
Cord Range	0.230"-0.720"(5.8-18.3)
Style	Standard
Color	Black and White
Item Type	Insulgrip® Plug
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Nylon
Specifications	Blade Holder - Nylon, Retainer - Polycarbonate, Cover - Nylon, Cord Clamp - Nylon, Contact Blades - Copper Alloy, Spring - Stainless Steel, Plunger - Nylon, Drive/Assembly/Cord Clamp Screws - Steel
UPC	783585719702

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	<ul style="list-style-type: none"> • Maximum continuous 75°C • minimum -40°C (w/o impact)
Operating Temperature	Maximum continuous 75°C and minimum without Impact -40

Horsepower - Maximum °C
1.5

Product Assets

- [Catalog \[English\]](#)
 - [Catalog Page \[English\]](#)
 - [Catalog Page \[English\]](#)
 - [Installation Manual \[English\]](#)
-



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
WDK-HBL4570CST-SPEC-EN | REV 1/2026