

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Plug, 60A 125/250V, 3-Pole 4-Wire Grounding, Watertight- Reversed Service



By Hubbell Wiring Device-Kellems
Catalog # [HBL460P12WR](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Plug, 60A 125/250V, 3-Pole 4-Wire Grounding, Terminal Screws, Orange, Watertight- Reversed Service

Features

- Gasketed sealing ring provides watertight seal
- Heavy duty external cord grips

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 3,000V AC Min, Electrical - Max. Working Voltage - 600V AC RMS, Environmental - Flammability - HB or Better per UL 94 or CSA C22.2 No. 0.17, Environmental - Ingress Protection - IP67 Suitability, Environmental - Moisture Resistance - Watertight per IEC 60309-1, Environmental - Operating Temperature - Maximum Continuous 75°C, Minimum - 40°C w/o impact, Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682, Mechanical - Product Identification - Identification and ratings are a permanent part of the device housing., Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

Specifications

| | |
|--------------------------|--|
| Environmental Conditions | Watertight |
| EU RoHS Indicator | Yes |
| Industry Standard(s) | <ul style="list-style-type: none"> • CSA Standard C22.2 No. 182.1 • UL Classified to IEC60309-1 • UL Listed, File E146032 |
| Nema Rating | Non-NEMA |

Conductor

| | |
|-----------------|------------------|
| Number Of Wires | 4-Wire |
| Wire Size | #8 AWG to #2 AWG |
| Number Of Poles | 3-Pole |

Configuration

| | |
|-----------|--------------|
| Cord Type | All Portable |
|-----------|--------------|

Current

| | |
|----------------|------|
| Current Rating | 60 A |
|----------------|------|

| | |
|----------------------------|--------------------------|
| Amperage Rating | 60 A |
| Voltage Rating Description | 120/240 VAC |
| Phase | Single Phase |
| Current / Amperage Rating | 60 A |
| Connectivity | Pressure Terminal Screws |
| Voltage Rating | 120/240 VAC |

Dimensions

| | |
|--------------|----------------|
| Display Size | Standard Sized |
|--------------|----------------|

General

| | |
|------------------------------|---|
| Series | Non-Fused |
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Style | Reverse Service |
| Color | Orange |
| Item Type | Male Plug- Reversed |
| Material - Mounting Hardware | Cord Mounted |
| Type | Watertight Mating Plug |
| Material | Composite |
| Specifications | <ul style="list-style-type: none"> • Contact Carrier - High-Impact Thermoset • Housing - Zytel® ST801 Nylon • Locking Ring - Reinforced Thermoplastic Polyester • Retainer - High-Impact Thermoset • Terminal Screws - Stainless Steel |

| | |
|-----|--------------|
| UPC | 783585012728 |
|-----|--------------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[French, English\]](#)