

Straight Blade Connector Body, Insulgrip Heavy Duty, Industrial/Commercial, Straight, 2- Pole 3-Wire Grounding, 15A 125V, 5-15R, Black, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5269CM2](#)

Straight Blade Devices, Female Connector Body, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2- Pole 3-Wire Grounding, 15A 125V, 5-15R, Black, Single Pack



Features

- Individual wiring terminals completely enclosed
- Powerful, offsetting cord grips clamp on individual conductors
- Fast lead assembly screws
- Beveled housing prevents snagging

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Nema Rating	5-15R

Conductor

Number Of Conductors	3-Wire Grounding
Conductor Range	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A
Current / Amperage Rating	15 A
Connectivity	Screw Terminals
Voltage Rating	125 VAC

Dimensions

Display Size	Standard
--------------	----------

General

Series	Insulgrip
OEM Brand Name	Hubbell Wiring Device-Kellems
Style	Standard
Color	Black
Item Type	Insulgrip
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Composite
UPC	783585848525

Logistics

Carton Quantity	10
Pallet Quantity	3600

Operational

Temperature Rating	<ul style="list-style-type: none">• Maximum Continuous: 75° C• Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[French\]](#)
- [Installation Manual \[Spanish\]](#)