

## Plug In Adapter, 15A 125V Crow Foot to 5-15R

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5289](#)

Plug In Adapter, 15A 125V Crow Foot to 5- 15R



### Features

- 15A 125V Crow Foot to 5- 15R

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	Non-NEMA

### Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

### Current

Current Rating	15 A
Amperage Rating	15 A
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Screw Terminals
Wattage	2500 Max
Voltage Rating	Multi-Rated kV

### Dimensions

Display Size Standard Sized Product

### General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	White
Item Type	Plug-In Adapter
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
Specifications	<ul style="list-style-type: none"><li>• Female end - 3 Wire 15A, 125V</li><li>• Male end - 3 wire crow foot 15A, 125V blades</li><li>• Product Type - Plug-In Adapters</li></ul>

UPC

783585809175

### Logistics

Carton Quantity 10

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)