

EdgeConnect™ Series, Straight Blade Devices, Plug, Corrosion Resistant, Industrial/Commercial/Commercial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Yellow and White



By Hubbell Wiring Device-Kellems
Catalog # [HBL52CM66CST](#)

EdgeConnect™, Straight Blade Devices, Plug, Corrosion Resistant, Industrial/Commercial/Commercial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Yellow and White

Features

- Spring termination for a faster and more secure terminal connection
- Ribbed housing is impact and chemical resistant
- Superior cord grip design protects terminations from excess strain
- Accepts #14 - #10AWG, solid or stranded

Application

Extra Heavy Duty Industrial/Commercial Grade

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 V-2, Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact), Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Contact Manufacturer
Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified to C22.2 No. 42 File 280 • Fed. Spec. W-C596G • NEMA® WD-6 Compliant • UL Listed to UL498 File E1718
Nema Rating	5-15P

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Conductors	3-Wire Grounding
Conductor Range	#14 AWG to #10 AWG

Number Of Poles 2-Pole

Configuration

Cord Type All Listed Portables

Current

Dielectric Strength Withstands 2,000V minimum
Phase Single Phase
Current / Amperage Rating 15 A
Connectivity Spring Termination
Voltage Rating 125 V

Dimensions

Display Size Standard Sized Product
Size 1.32 in x 0.83 in x 3.28 in
Weight 0.2 lb.

General

Series EdgeConnect™ Series
Cord Range 0.230"-0.720"(5.8-18.3)
Style Standard
Color Yellow and White
Item Type Insulgrip® Plug
Insulation Insulated Body
Material - Mounting Hardware Cord Mounted
Type Plugs
Material Nylon
Specifications Blade Holder - Nylon, Retainer - Polycarbonate, Cover - Nylon, Cord Clamp - Nylon, Contact Blades - Nickel Plated Copper Alloy, Spring - Stainless Steel, Plunger - Nylon, Drive/Assembly/Cord Clamp Screws - Stainless Steel
UPC 783585796215

Logistics

Carton Quantity 10

Operational

Temperature Rating	<ul style="list-style-type: none">• Maximum continuous 75°C• minimum -40°C (w/o impact)
Operating Temperature	Maximum continuous 75°C and minimum without Impact -40°C
Horsepower - Maximum	0.5

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[English\]](#)



A Hubbell brand