

## EdgeConnect™ Series, Straight Blade Devices, Plug, Corrosion Resistant, Industrial/Commercial/Commercial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20P, Yellow and White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL53CM66CST](#)

EdgeConnect™, Straight Blade Devices, Plug, Corrosion Resistant, Industrial/Commercial/Commercial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20P, Yellow and White



### Features

- Spring termination for a faster and more secure terminal connection
- Ribbed housing is impact and chemical resistant
- Superior cord grip design protects terminations from excess strain
- Accepts #14 - #10AWG, solid or stranded

### Application

Extra Heavy Duty Industrial/Commercial Grade

### Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 V-2, Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact), Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Contact Manufacturer
Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified to C22.2 No. 42 File 280</li> <li>• Fed. Spec. W-C596G</li> <li>• NEMA® WD-6 Compliant</li> <li>• UL Listed to UL498 File E1719</li> </ul>
Nema Rating	5-20P

### Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Conductors	3-Wire Grounding
Conductor Range	#14 AWG to #10 AWG

Number Of Poles 2-Pole

### Configuration

Cord Type All Listed Portables

### Current

Dielectric Strength Withstands 2,000V minimum  
Phase Single Phase  
Current / Amperage Rating 20 A  
Connectivity Spring Termination  
Voltage Rating 125 V

### Dimensions

Display Size Standard Sized Product  
Size 1.32 in x 0.83 in x 3.28 in  
Weight 0.2 lb.

### General

Series EdgeConnect™ Series  
Cord Range 0.230"-0.720"(5.8-18.3)  
Style Standard  
Color Yellow and White  
Item Type Insulgrip® Plug  
Insulation Insulated Body  
Material - Mounting Hardware Cord Mounted  
Type Plugs  
Material Nylon  
Specifications Blade Holder - Nylon, Retainer - Polycarbonate, Cover - Nylon, Cord Clamp - Nylon, Contact Blades - Nickel Plated Copper Alloy, Spring - Stainless Steel, Plunger - Nylon, Drive/Assembly/Cord Clamp Screws - Stainless Steel  
UPC 783585796222

### Logistics

Carton Quantity 10

### Operational

Temperature Rating	<ul style="list-style-type: none"><li>• Maximum continuous 75°C</li><li>• minimum -40°C (w/o impact)</li></ul>
Operating Temperature	Maximum continuous 75°C and minimum without Impact -40°C
Horsepower - Maximum	1

### Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[English\]](#)



A Hubbell brand