

Adapter, Marine, Molded, Straight Blade, 30A 125V Locking Female L5-30R to 15A 125V 5-15P Straight Blade Male, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL61CM22](#)

Adapter, Marine, Molded, Straight Blade, 30A 125V Locking Female L5-30R to 15A 125V 5-15P Straight Blade Male, Yellow



Features

- New quick connect with backwards compatibility

Application

Straight Adapter

Specifications

EU RoHS Indicator No

Configuration

Number Of Pins Male- 15A 125V Straight Blade

Current

Amperage Rating 30 A
Wattage 3750
Voltage Rating 125 VAC

General

OEM Brand Name Hubbell Wiring Device-Kellems
Color Yellow
Receptacle Type Female- 30A 125V Twist-Lock®
Material Composite

Specifications

- Adapter Style - Straight (Pig Tail)
 - Female End Rating - 30A 125V, 2P3W Twist-Lock®
 - Male End Rating - 15 or 20A 125V, 2P3W Straight Blade
 - Poles and Wires - 2 Pole, 3 Wire Grounding
 - Product Type - Adapters
- 783585808598

UPC

Logistics

Carton Quantity 10
Pallet Quantity 252

Operational

Operating Temperature Max Continuous- 75 Degrees C,
Minimum- -40 Without Impact

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[English\]](#)