

Adapter, Marine, Molded, Straight Blade, 30A 125V Locking Female L5-30R to 50A 125V Locking Male, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL61CM55](#)

Marine Adapter Molded, Straight Blade 30A Locking Female to
50A Locking Male

Features

- Marine
- Molded
- Straight Blade
- 30A 125V Locking Female L5-30R to 50A 125V Locking Male

Application

Straight Adapter

Specifications

EU RoHS Indicator No
Standards - RoHS Compliance CM
Status

Configuration

Number Of Pins Male- 50A 125V Twist-Lock®

Current

Amperage Rating 30 A
Wattage 3750
Voltage Rating 125 VAC

General

OEM Brand Name Hubbell Wiring Device-Kellems



Color	Yellow
Receptacle Type	Female- 30A 125V Twist-Lock®
Material	Composite
Specifications	<ul style="list-style-type: none">• Adapter Style - Straight (Pig Tail)• Female End Rating - 30A 125V, 2P3W Twist-Lock®• Male End Rating - 50A 125V, 2P3W Twist-Lock®• Poles and Wires - 2 Pole, 3 Wire Grounding• Product Type - Adapters
UPC	783585808628

Logistics

Carton Quantity 1

Operational

Operating Temperature Max Continuous- 75 Degrees C,
Minimum- -40 Without Impact

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[English\]](#)