

Adapter, Marine, Molded, Straight Blade, 30A 125V, 2-Pole 3-Wire Grounding Female to 50A 125/250V, 3-Pole 4-Wire Grounding Locking Male

By Hubbell Wiring Device-Kellems
Catalog # [HBL61CM71](#)

Marine Adapter Molded, Straight Blade 30A Female to 50A Locking Male



Features

- Marine
- Molded
- Straight Blade
- 30A 125V

Application

Straight Adapter

Specifications

EU RoHS Indicator	No
Standards - RoHS Compliance Status	CM

Configuration

Number Of Pins	Male- 50A 125/250V Twist-Lock®
----------------	--------------------------------

Current

Amperage Rating	30 A
Wattage	7500
Voltage Rating	125/250 VAC

General

OEM Brand Name	Hubbell Wiring Device-Kellems
----------------	-------------------------------

Color

Yellow

Receptacle Type

Female- 30A 125V Twist-Lock®

Material

Composite

Specifications

- Adapter Style - Straight (Pig Tail)
- Female End Rating - 30A 125V, 2P3W Twist-Lock®
- Male End Rating - 50A 125/250V, 3P4W Twist-Lock®
- Poles and Wires - 2 Pole, 3 Wire Grounding
- Product Type - Adapters

UPC

783585808680

Logistics

Carton Quantity	1
Pallet Quantity	126

Operational

Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
-----------------------	--

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[English\]](#)