

Adapter, Marine, Molded Straight, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL61CM72](#)

Marine Adapter Molded Straight Blade



Features

- Marine
- Molded Straight
- Yellow

Application

Straight Adapter

Specifications

EU RoHS Indicator No
Standards - RoHS Compliance CM
Status

Configuration

Number Of Pins Male- 50A 125/250V Twist-Lock®

Current

Amperage Rating 50 A
Wattage 12500
Voltage Rating 125/250 VAC

General

OEM Brand Name Hubbell Wiring Device-Kellems

Color

Yellow

Receptacle Type

Female- 50A 125V Twist-Lock®

Material

Composite

Specifications

- Adapter Style - Straight (Pig Tail)
 - Female End Rating - 50A 125V, 2P3W Twist-Lock®
 - Male End Rating - 50A 125/250V, 3P4W Twist-Lock®
 - Poles and Wires - 2 Pole, 3 Wire Grounding
 - Product Type - Adapters
- 783585808697

UPC

Logistics

Carton Quantity

1

Operational

Operating Temperature

Max Continuous- 75 Degrees C,
Minimum- -40 Without Impact

Product Assets

[Catalog \[English\]](#)

[Catalog Page \[English\]](#)

[Catalog Page \[English\]](#)

[Installation Manual \[English\]](#)