

## Adapter, Marine Adapter, Molded "Y", 2) 30A 125V Locking Female L5-30R to 50A 125/250V Locking Male, 4-Pole 4- Wire Grounding, Yellow



By Hubbell Wiring Device-Kellems  
Catalog # [HBL64CM54](#)

Marine Adapter, Molded "Y", Two 30A Locking Female to 50A Locking Male

### Features

- Molded "Y"
- 2) 30A 125V Locking Female L5-30R to 50A 125/250V Locking Male
- 4-Pole 4- Wire Grounding

### Application

"Y" Adapter

### Specifications

EU RoHS Indicator No

### Configuration

Number Of Pins Male- 50A 125/250V Twist-Lock®

### Current

Amperage Rating 30 A  
Wattage 7500  
Voltage Rating 125/250 VAC

### General

OEM Brand Name Hubbell Wiring Device-Kellems  
Color Yellow

Receptacle Type  
Material  
Specifications

Female- 30A 125V Twist-Lock® Composite

- Adapter Style - Y Adapter
- Female End Rating - 30A 125V, 2p3w Twist-Lock®
- Male End Rating - 50A 125/250V, 3P4W Twist-Lock®
- Poles and Wires - Female Side- 2P3W Grounding, Male Side 3P4W Grounding
- Product Type - Adapters

783585808772

UPC

### Logistics

Carton Quantity 1  
Pallet Quantity 126

### Operational

Operating Temperature Max Continuous- 75 Degrees C,  
Minimum- -40 Without Impact

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)  
[Catalog Page \[English\]](#)  
[Installation Manual \[English\]](#)