

Adapter, Marine Adapter, Molded "Y", 2) 30A 125V Locking Female L5-30R to 30A 125 Locking Male, 2-Pole 3-Wire Grounding, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL64CM56](#)

Marine Adapter, Molded "Y", Two 30A Locking Female to 30A Locking Male

Features

- Molded "Y"
- 2) 30A 125V Locking Female L5-30R to 30A 125 Locking Male
- 2-Pole 3-Wire Grounding

Application

"Y" Adapter

Specifications

EU RoHS Indicator No

Configuration

Number Of Pins Male- 30A 125V Twist-Lock®

Current

Amperage Rating 30 A
Wattage 3750
Voltage Rating 125 VAC

General

OEM Brand Name Hubbell Wiring Device-Kellems
Color Yellow
Receptacle Type Female- 30A 125V Twist-Lock®



Material Specifications

UPC

Logistics

Carton Quantity 1
Pallet Quantity 126

Operational

Operating Temperature Max Continuous- 75 Degrees C,
Minimum- -40 Without Impact

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[English\]](#)

Composite

- Adapter Style - Y Adapter
 - Female End Rating - 30A 125V, 2P3W Twist-Lock®
 - Male End Rating - 30A 125V, 2P3W Twist-Lock®
 - Poles and Wires - 2 Pole, 3 Wire Grounding
 - Product Type - Adapters
- 783585808796