

Straight Blade Devices, Plug Strip, 6) Receptacles, Metallic Body, 6' Cord

By Hubbell Wiring Device-Kellems
Catalog # [HBL6MPS](#)

Straight Blade Devices, Plug Strip, 6) Receptacles, Metallic Body, 6' Cord



Features

- Office White color for aesthetics and metal housing
- 6 foot cord
- wire management

Application

Standard Devices

Specifications

Environmental Conditions Indoor Dry Unless Protected By Additional Means

EU RoHS Indicator No

Conductor

Cord Length 6 ft

Configuration

Number Of Outlets 6

Current

Current Rating 15 A

Frequency Rating 60 Hz

Phase Single Phase

Current / Amperage Rating 15 A

Connectivity Plug-In

Dimensions

Display Size 0 Joules

General

Series

Economy Power Strips (no SPD)

OEM Brand Name

Hubbell Wiring Device-Kellems

Outlet

Straight Blade 5-15R

Color

Office White

Item Type

Surge Protection Plug Strips

Material - Mounting Hardware

Portable

Type

Metallic

Material

Steel

Specifications

- Height - 1.5" (38.1)

- Length - 12.25" (311.2)

- No.of Outlets - 6

- Width - 2.5" (63.5)

UPC

783585120669

Logistics

Carton Quantity

20

Pallet Quantity

400

Operational

Response Time

5

Indicator(s) Type

LED Indicator

Operating Temperature

32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

Product Assets

[Catalog \[English\]](#)

[Catalog Page \[English\]](#)

[Catalog Page \[English\]](#)

[Installation Manual \[Spanish, French, English\]](#)