

## Straight Blade Devices, Plug Strip, 6) Receptacles, Plastic Body, 6' Cord, Office White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL6PPS](#)

Straight Blade Devices, Plug Strip, 6) Receptacles, Plastic Body,  
6' Cord, Office White



### Features

- 6 foot cord
- Tamper resistant shutters.

### Application

6 Outlet, Standard Devices

### Specifications

Environmental Conditions Indoor Dry Unless Protected By  
Additional Means

EU RoHS Indicator Yes

### Conductor

Cord Length 6 ft

### Configuration

Number Of Outlets 6

### Current

Current Rating 15 A

Frequency Rating 60 Hz

Phase Single Phase

Current / Amperage Rating 15 A

Connectivity Plug-In

### Dimensions

Display Size 0 Joules

### General

### Series

Economy Power Strips (no  
SPD)

OEM Brand Name

Hubbell Wiring Device-Kellems

Outlet

Straight Blade 5-15R

Color

Office White

Item Type

Surge Protection Plug Strips

Material - Mounting Hardware

Portable

Type

Non-Metallic

Material

Non-Metallic

Specifications

- Height - 1.85" (47.0)

- Length - 11.2" (284.5)

- No.of Outlets - 6

- Width - 2.36" (59.9)

UPC

783585120508

### Logistics

Carton Quantity

12

Pallet Quantity

480

### Operational

Response Time

5

Indicator(s) Type

LED Indicator

Operating Temperature

32 Deg F to 140 Deg F (0 Deg  
C to 60 Deg C)

### Product Assets

[Catalog \[English\]](#)

[Catalog Page \[English\]](#)

[Installation Manual \[Spanish, French, English\]](#)