

## Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 6 Outlet, 350 Joules, 6' Cord, Yellow

By Hubbell Wiring Device-Kellems  
Catalog # [HBL6PS350YL](#)

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 6 Outlet, 350 Joules, 6' Cord, Yellow



### Features

- Yellow color for high visibility and metal housing
- 350 joules, 6 foot cord, wire management

### Application

Standard Devices and Cord Holder

### Performance

Electrical - Max Surge Current - 6.5kA, Electrical - Max. Operating Voltage - 130, Electrical - Operating Frequency - 50/60Hz, Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C)

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Standards - RoHS Compliance Status	CM

### Conductor

Cord Length	6 ft
-------------	------

### Configuration

Number Of Outlets	6
-------------------	---

### Current

Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Plug-In

### Dimensions

Display Size	350 Joules
--------------	------------

### General

Series	Economy Surge Strips
OEM Brand Name	Hubbell Wiring Device-Kellems
Outlet	Straight Blade 5-15R
Color	Yellow
Item Type	Surge Protection Plug Strips
Material - Mounting Hardware Type	Portable Metallic
Material Specifications	Non-Metallic <ul style="list-style-type: none"><li>• Color - Yellow</li><li>• Housing - Metal</li><li>• Length - 14.75" (374.7)</li><li>• Width - 1.85" (47.0)</li><li>• Width - 2.5" (63.5)</li></ul>

### UPC

783585120607

### Logistics

Carton Quantity	12
-----------------	----

### Operational

Response Time	5
Indicator(s) Type	LED Indicator
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

### Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[Spanish, French, English\]](#)