

Surge Protective Devices, SPIKESHIELD
TVSS Plug Strips, 15A 125V, 7 Outlet with
Telephone/Fax, 150 Joules, 6' Cord, Office
White

By Hubbell Wiring Device-Kellems
Catalog # [HBL7PS1050MA](#)

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A
125V, 7 Outlet with Telephone/Fax, 150 Joules, 6' Cord, Office
White

Features

- 1050 joule, 6 foot cord, \$5,000 down-line warranty
- Tamper tamper resistant shutters.

Performance

Electrical - Max Surge Current - 19.5kA, Electrical - Max.
Operating Voltage - 130, Electrical - Operating Frequency -
50/60Hz, Environmental - Operating Temperature - -40°F to
160°F (-40°C to 70°C)

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes

Conductor

Cord Length	6 ft
-------------	------

Configuration

Number Of Outlets	7
-------------------	---

Current

Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Plug-In

Dimensions



Display Size	1050 Joules
--------------	-------------

General

Series	Economy Surge Strips
OEM Brand Name	Hubbell Wiring Device-Kellems
Outlet	Straight Blade 5-15R
Color	Office White
Item Type	Surge Protection Plug Strips
Material - Mounting Hardware	Portable
Type	Non-Metallic
Material	Non-Metallic
Specifications	• Color - Off. White • Height - 1.85" (47.0) • Housing - ABS • Length - 14.75" (374.7) • Width - 2.36" (59.9)

UPC	783585120577
-----	--------------

Logistics

Carton Quantity	12
-----------------	----

Operational

Response Time	5
Indicator(s) Type	LED Indicator
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)