

## EdgeConnect™ Series, Straight Blade Devices, Plug, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Clear

By Hubbell Wiring Device-Kellems  
Catalog # [HBL8215CTST](#)



EdgeConnect™, Straight Blade Devices, Plug, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Clear

### Features

- Spring termination for a faster and more secure terminal connection
- Ribbed housing is impact and chemical resistant
- Superior cord grip design protects terminations from excess strain
- Accepts #14 - #10AWG, solid or stranded

### Application

Hospital Grade

### Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 V-2, Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact), Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Contact Manufacturer
Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified to C22.2 No. 42 File 280</li> <li>• Fed. Spec. W-C596G</li> <li>• NEMA® WD-6 Compliant</li> </ul>
Nema Rating	5-15P

### Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Conductors	3-Wire Grounding
Conductor Range	#14 AWG to #10 AWG
Number Of Poles	2-Pole

### Configuration

Cord Type	All Listed Portables
-----------	----------------------

### Current

Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Spring Termination
Voltage Rating	125 V

### Dimensions

Display Size	Standard Sized Product
Size	3.28 in x 1.57 in x 1.07 in
Weight	0.2 lb.

### General

Series	EdgeConnect™ Series
Cord Range	0.230"-0.720"(5.8-18.3)
Style	Standard
Color	Clear
Item Type	Insulgrip® Plug
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Nylon
Specifications	Blade Holder - Nylon, Retainer - Polycarbonate, Cover - Nylon, Cord Clamp - Nylon, Contact Blades - Copper Alloy, Spring - Stainless Steel, Plunger - Nylon, Drive/Assembly/Cord Clamp Screws - Steel
UPC	783585964881

### Logistics

Carton Quantity	10
-----------------	----

### Operational

Temperature Rating	<ul style="list-style-type: none"> <li>• Maximum continuous 75°C</li> <li>• minimum -40°C (w/o impact)</li> </ul>
Operating Temperature	Maximum continuous 75°C and minimum without Impact -40 °C
Horsepower - Maximum	0.5

## Product Assets

[Catalog \[English\]](#)

[Catalog Page \[English\]](#)

[Catalog Page \[English\]](#)

[Catalog Page \[English\]](#)

[Installation Manual \[English\]](#)

---



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved  
WDK-HBL8215CTST-SPEC-EN | REV 1/2026