

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 8-Outlet with Telephone/Satellite, 2100 Joules, 6' Cord, Office White

By Hubbell Wiring Device-Kellems
Catalog # [HBL8PS2100DA](#)



Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 8-Outlet with Telephone/Satellite, 2100 Joules, 6' Cord, Office White

Features

- 1050 joule, 6 foot cord, \$5,000 down-line warranty
- Tamper tamper resistant shutters.

Specifications

EU RoHS Indicator No

Current

Phase	Single Phase
Connectivity	Plug-In
Amperage Rating	15 A
Frequency Rating	60 Hz
Voltage Rating	125 VAC

General

Material - Mounting Hardware	Portable
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Non-Metallic
Specifications	<ul style="list-style-type: none">• Color - Off. White

- Cord Length - 6 Inch
- Housing - ABS
- Joule Rating - 2100
- No.of Outlets - 8

UPC
Outlet

783585120591
Straight Blade 5-15R

Logistics

Carton Quantity 20

Operational

Indicator(s) Type	LED Indicator
Response Time	5
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)