

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 8-Outlet with Telephone/Fax, 2100 Joules, 6' Cord, Office White



By Hubbell Wiring Device-Kellems
Catalog # [HBL8PS2100MA](#)

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 8-Outlet with Telephone/Fax, 2100 Joules, 6' Cord, Office White

Features

- 1050 joule, 6 foot cord, \$5,000 down-line warranty
- Tamper tamper resistant shutters.

Performance

Electrical - Max Surge Current - 39.0kA, Electrical - Max. Operating Voltage - 130, Electrical - Operating Frequency - 50/60Hz, Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C)

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes

Conductor

Cord Length	6 ft
-------------	------

Configuration

Number Of Outlets	8
-------------------	---

Current

Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Plug-In

Dimensions

Display Size	2100 Joules
--------------	-------------

General

Series	Economy Surge Strips
OEM Brand Name	Hubbell Wiring Device-Kellems
Outlet	Straight Blade 5-15R
Color	Office White
Item Type	Surge Protection Plug Strips
Material - Mounting Hardware	Portable
Type	Non-Metallic
Material	Non-Metallic
Specifications	<ul style="list-style-type: none">• Color - Off. White• Cord Length - 6 Inch• Housing - ABS• Joule Rating - 2100• No.of Outlets - 8

UPC

783585120584

Logistics

Carton Quantity	20
Pallet Quantity	504

Operational

Response Time	5
Indicator(s) Type	LED Indicator
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[Spanish, French, English\]](#)