

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 8-Outlet, 350 Joules, 6' Cord, Office White

By Hubbell Wiring Device-Kellems
Catalog # [HBL8PS350YL](#)

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 8-Outlet, 350 Joules, 6' Cord, Office White



Features

- Yellow color for high visibility and metal housing
- 350 joules, 6 foot cord, wire management

Application

Standard Devices and Cord Holder

Performance

Electrical - Max Surge Current - 6.5kA, Electrical - Max. Operating Voltage - 130, Electrical - Operating Frequency - 50/60Hz, Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C)

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Standards - RoHS Compliance Status	CM

Conductor

Cord Length	6 ft
-------------	------

Configuration

Number Of Outlets	6
-------------------	---

Current

Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Plug-In

Dimensions

Display Size	350 Joules
--------------	------------

General

Series	Economy Surge Strips
OEM Brand Name	Hubbell Wiring Device-Kellems
Outlet	Straight Blade 5-15R
Color	Yellow
Item Type	Surge Protection Plug Strips
Material - Mounting Hardware Type	Portable Metallic
Material Specifications	Non-Metallic

- Color - Yellow
- Height - 1.85" (47.0)
- Housing - Metal
- Length - 10.0" (254.0)
- Width - 6.0" (152.4)

UPC	783585120614
-----	--------------

Logistics

Carton Quantity	12
Pallet Quantity	360

Operational

Response Time	5
Indicator(s) Type	LED Indicator
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)