

Straight Blade Devices, Male Plug, Insulgrip, Heavy Duty, Industrial/Commercial Grade, Straight, 3-Pole 3-Wire Non-Grounding, 30A 125/250V, 10-30P.



By Hubbell Wiring Device-Kellems
Catalog # [HBL9337C](#)

Straight Blade Devices, Male Plug, Insulgrip, Nylon, Heavy Duty, Industrial/Commercial Grade, Straight, 3-Pole 3-Wire Non-Grounding, 30A 125/250V, 10-30P, Black, Single Pack.

Features

- Supertough nylon housing
- Gripping ribs provide secure gripping area
- Captive Allen head terminal screws are user-ready

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 HB, Environmental - IP Suitability - IP20, Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact), Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #12 AWG through #4 AWG copper wire only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Specifications

EU RoHS Indicator	Contact Manufacturer
Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified • UL Listed File E1706
Nema Rating	10-30P

Conductor

Number Of Wires	3-Wire
Wire Size	#12 AWG to #4 AWG
Number Of Poles	3-Pole

Current

Dielectric Strength	Withstands 2,000V minimum
Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	125/250 V
Current / Amperage Rating	30 A
Wattage	7500 W
Voltage Rating	<ul style="list-style-type: none"> • 125 V

- 250 V

Dimensions

Length	4.13 in
Width	2.75 in
Weight	0.8 lb.
Height	2.88 in
Dimensions	4.13 in x 2.75 in x 2.88 in

General

Series	Extra Heavy Duty
Cord Range	0.625"-1.00"
Style	Non-Grounding
Color	Black
Type	Plug
Material	Nylon
Specifications	<ul style="list-style-type: none"> • Blade Holder - Reinforced Thermoplastic Polyester • Blades - Brass • Box Terminals - Copper Alloy • Cord Clamps - Reinforced Thermoplastic Polyester • Housing - Supertough Nylon
UPC	783585015699

Logistics

Carton Quantity	5
-----------------	---

Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Horsepower - Maximum	2

Product Assets

[Catalog \[English\]](#)