

Disconnect Switches, Sloped Enclosure, 30A 600V AC, Non-Fused, NEMA 4X, Stainless Steel, With 5' Pre-Wired Female Cable

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS3SSRMQ5](#)

Disconnect Switches, Sloped Enclosure, 30A 600V AC, Non-Fused, NEMA 4X, Stainless Steel, With 5' Pre-Wired Female Cable



Features

- Sloped Enclosure
- 30A 600V AC
- Non-Fused
- NEMA 4X

Performance

Electrical - Dielectric Voltage - 2,200V AC minimum for 1 minute, Electrical - Electrical Life - 6,000 cycles with load, Electrical - Max. Working Voltage - 600V AC RMS, Environmental - Flammability - UL94-5VA and V0 Classification, Environmental - Operating Temperature - Max. continuous 75°C, Min. continuous -40°C, Mechanical - Impact Resistance - UL746C, Mechanical - Mechanical Life - 10,000 minimum cycles, Mechanical - Terminal Accommodations - 30A, #14 AWG Min. - #10 AWG Max, Mechanical - Terminal Torque - 30A, 20 inch pounds

Specifications

Industry Standard(s)	<ul style="list-style-type: none"> • Listed to UL 2238 and UL 50E • UL 508, Industrial Control Equipment File #E36355
EU RoHS Indicator	Contact Manufacturer

Conductor

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

Current

Phase	Three Phase
Dielectric Strength	2,200V AC minimum for 1 minute
Connectivity	Pre-Wired
Current Rating	30 A
Amperage Rating	30 A

Dimensions

Width	6 in
Height	4.12 in
Length	8.5 in
Dimensions	8.5 in x 6 in x 4.12 in

General

Type	Disconnect Switches
Enclosure Type	Type 4X
Series	MotorQuick/LINKOSITY
UPC	783585541570
Ingress Protection	IP67

Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Horsepower - Maximum	15

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)