

Switched Disconnects and Enclosures Stainless Steel Replacement Covers

HUBBELL

Features

- Formed in nonporous 304 stainless steel
- IP69k and Type 4X, 12K water ingress protection
- Certified by NSF for hygiene in food processing applications
- Highly visible red handle which meets OSHA Lockout/Tagout capabilities

Ordering Information

Description	UPC Number	Catalog Number
30A Replacement Cover for sloped top disconnect switch	783585550978	HBLDS3SSRRC

Specifications

Cover & Hardware	Stainless Steel
Handle & Mount	PBT

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current and voltage
Dielectric Voltage Max. Working Voltage	Withstands 3000V AC minimum 600V AC RMS
Mechanical	
Impact Resistance	In accordance with UL 746C
Mounting	Feet are fixed
Terminal Identification	In accordance with UL, CSA and international conventions
Environmental	
Flammability	UL94-5VA and V0 Classification
Indoor and Outdoor – Type 4X (Wash down, Corrosion resistant); Indoor – Type 12 (Dust-tight, Falling Dirt, Noncorrosive Liquids).	Max. Continuous: 75°C; Min. Continuous: -40°C without impact
Moisture Resistance	Indoor and Outdoor – Type 4X (Wash down, Corrosion resistant); Indoor – Type 12 (Dust-tight, Falling Dirt, Noncorrosive Liquids).
Operating Temperature	Max. Continuous: 75°C; Min. Continuous: -40°C without impact



Complementary Products

Stainless Steel Circuit-Lock® Unfused Switched Disconnect	HBLDS3SSR; HBLDS3SSR2K; HBLDS3SSRVFD; HBLDS3SSRAC
-----------------------------------------------------------	---------------------------------------------------------

Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

