

Locking Devices Insul-Lock Plus Devices 20A Panel Mount

HUBBELL

Features

- Impact resistant thermoplastic construction
- Panel mount devices accept commonly available .25" flat tab style connectors
- UL Enclosure type 4X and IP65 rated
- Disconnectable under load
- Industry standard mating

Ordering Information

Description Outlet, 1/4" tab terminations with divider	UPC 783585580906	Catalog Number HBLFPD
Termination .25" flat tab style connectors	Color Black and Yellow	

Listings

cULus
UL50E Encl. type 4X when used in combination with covers HBLFPC or HBLFPDC
or with when mated to HBLMC
IP65 rated when used in combination with covers HBLFPC or HBLFPDC or with
when mated to HBLMC

Specifications

Body	Thermoplastic
Contacts	Copper Alloy
Weight	0.1

Performance

Electrical	
Amperage	20A
Voltage	up to 250V AC



Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

