

Temporary Power Temporary Industrial Lighting Fluorescent Light String

HUBBELL

Features

- Inline on/off switch for ease of operation
- 120V AC electronic ballast protected by light fixture

Ordering Information

| | | |
|--|--------------|----------------|
| Description | UPC | Catalog Number |
| Fluorescent light string, 48.5" single fixture w/ hanging straps | 783585467467 | HBLFS2549 |

Listings

UL
CSA
ETL

Specifications

| | |
|------------|-------------|
| Light Type | Fluorescent |
| Plug Type | NEMA 5-15P |
| Length | 48.5 |
| Width | 2.625 |

Performance

| | |
|-------------------|----------|
| Electrical | |
| Lamp Life | 20,000 |
| Light Color | 4100 K |
| Lumen Output | 2125 |
| Rating | 15A 125V |
| Wattage | 25 |

| | |
|-------------------|--------------|
| Mechanical | |
| Cord Length | 6 ft. |
| Cord Type | 16 AWG SJTOW |



Online Resources

[eCatalog](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

