

Features

- Ceiling trim mounting plate and scuff boot included
- All conductors are #12 AWG stranded copper
- Ready for quick installation
- UL Listed

Ordering Information

Style	Color/Finish	Catalog Number	UPC Number
(1) 20A Orange IG duplex, (1) Duplex	Office White finish	HBLPP10IGOW	783585483993



Listings

UL Listed

Specifications

Circuits	2 Circuits
----------	------------

Dimensions- inches (mm)

Length	10'2" (3100)
Width	2.13" (54)
Depth	2.1" (54)

Characteristics

Ceiling Trim plate	Included
Divider	Included
Scuff Boot	Included

Accessories

Adjustable T-bar bracket	ATB
Replacement trim kit	PPTRIM1

Online Resources

[Delivery Systems Guide](#)
[eCatalog](#)
[Product Drawing](#)
[Service Poles Guide](#)