

Features

- Ceiling trim mounting plate and scuff boot included
- All conductors are #12 AWG stranded copper
- Ready for quick installation
- UL Listed

Ordering Information

Style	Color/Finish	Catalog Number	UPC Number
(2) 20A Orange IG duplex, (1) IG surge supression duplex	Office White finish	HBLPP10SOW	783585476049



Listings

UL Listed

Specifications

Circuits	1 Circuit
----------	-----------

Dimensions- inches (mm)

Length	10'2" (3100)
Width	2.13" (54)
Depth	2.1" (54)

Characteristics

Ceiling Trim plate	Included
Divider	Included
Scuff Boot	Included

Accessories

Replacement trim kit	PPTRIM1
Adjustable T-bar bracket	ATB

Online Resources

- Delivery Systems Guide
- eCatalog
- Product Drawing
- Service Poles Guide