

Heavy Duty Products, IEC Pin and Sleeve, Plug, Switched, 60A 125V, 2-Pole 3-Wire, NEMA 4X/IP 69K,

By Hubbell Wiring Device-Kellems
Catalog # [HBL360P4W](#)



Heavy Duty IEC Pin and Sleeve, Plug, Switched, 60A 125V, 2-Pole 3-Wire, NEMA 4X/IP 69K,

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

General

| | |
|-----------------|------------------------|
| Catalog Number | HBL360P4W |
| Color | Yellow |
| Number Of Poles | 2-Pole |
| Series | Advantage Switch-Rated |
| Style | IP69k NEMA 4X |
| Type | Watertight Plug |
| UPC | 783585478982 |

Electrical Ratings

| | |
|----------------------------|---------|
| Amperage Rating | 60 A |
| Current / Amperage Rating | 60 A |
| Voltage Rating | 125 VAC |
| Voltage Rating Description | 125 VAC |

Conductor Related

| | |
|-----------------|--------|
| Number Of Wires | 3-Wire |
|-----------------|--------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL360P4W AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1303_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_HBL360P4W_DRAWINGS_PDF](#)
- [Specifications - HBL360P4W](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Advantage Series Switch-Rated Pin & Sleeve](#)