

Heavy Duty Products, IEC Pin and Sleeve, Plug, Switched, 60A 480V AC, 2-Pole 3-Wire, NEMA 4X/IP 69K

By Hubbell Wiring Device-Kellems
Catalog # [HBL360P7W](#)



Heavy Duty IEC Pin and Sleeve, Plug, Switched, 60A 480V AC, 2-Pole 3-Wire, NEMA 4X/IP 69K

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

General

Catalog Number	HBL360P7W
Color	Red
Number Of Poles	2-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Plug
UPC	783585479002

Electrical Ratings

Amperage Rating	60 A
Current / Amperage Rating	60 A
Voltage Rating	480 VAC
Voltage Rating Description	480 VAC

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBL360P7W AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1303_INSTALLINST](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_HBL360P7W_DRAWINGS_PDF](#)
[Specifications - HBL360P7W](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Advantage Series Switch-Rated Pin & Sleeve](#)