

Heavy Duty Products, IEC Pin and Sleeve, Inlet, Switched, 60/63A 125/250V, 3-Pole 4-Wire Grounding, NEMA 4X/IP69K

By Hubbell Wiring Device-Kellems
Catalog # [HBL5460B9W](#)

IEC Pin and Sleeve Switched Inlet, 60/63A

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

Conductor

Number Of Wires 4-Wire
Number Of Poles 3-Pole

Current



Current / Amperage Rating	60/63 A
Amperage Rating	60/63 A
Voltage Rating Description	3 Phase 250 VAC
Voltage Rating	3 Phase 250 VAC

General

Type	Watertight Inlet
Series	Advantage® Series
UPC	783585479293
Style	IP69k NEMA 4X
Color	Blue

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[French, English\]](#)