

## Heavy Duty Products, IEC Pin and Sleeve, Inlet, Switched, 60/63A 125/250V, 3-Pole 4-Wire Grounding, NEMA4X/IP69K, With Pilot Contact

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5460B9WP](#)



Heavy Duty IEC Pin and Sleeve, Inlet, Switched, 60/63A 125/250V, 3-Pole 4-Wire Grounding, NEMA4X/IP69K, with Pilot Contact

### Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

### General

Catalog Number	HBL5460B9WP
Color	Blue
Number Of Poles	3-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Inlet w/ Pilot Pin
UPC	783585479439

### Electrical Ratings

Amperage Rating	60/63 A
Current / Amperage Rating	60/63 A
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC

### Conductor Related

Number Of Wires	4-Wire
-----------------	--------

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - HBL5460B9WP AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD1304\\_INSTALLINST](#)  
[Literature - PULP & PAPER SOLUTIONS](#)  
[Literature - IEC Pin & Sleeve Devices](#)  
[Literature - Pulp & Paper Solutions](#)  
[Sales Drawings - WDK\\_HBL5460B\\_DRAWING\\_PDF](#)  
[Specifications - HBL5460B9WP](#)  
[Warranty - Industrial & Commercial Products](#)