

Heavy Duty Products, IEC Pin and Sleeve, Inlet, Switched, 60A 3-Phase 347/600V AC, 4-Pole 5-Wire Grounding, NEMA4X/IP69K

By Hubbell Wiring Device-Kellems
Catalog # [HBL560B5W](#)

IEC Pin and Sleeve Switched Inlet, 60A

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

Conductor

Number Of Wires 5-Wire
Number Of Poles 4-Pole

Current



Current / Amperage Rating	60 A
Amperage Rating	60 A
Voltage Rating Description	3 Phase Y 347/600 VAC
Voltage Rating	3 Phase Y 347/600 VAC

General

Type	Watertight Inlet
Series	Advantage® Series
UPC	783585479309
Style	IP69k NEMA 4X
Color	Black

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[French, English\]](#)