

Signal And Control Products, Field
Attachable Mini-Quick Male Plug, Right
Angled, 4-Pole

By Hubbell Wiring Device-Kellems
Catalog # [HCMA03F9](#)

Signal And Control Products, Field Attachable Mini-Quick Male
Plug, Right Angled, 4-Pole

Features

- Superior Contact Design
- Body with High Impact Design
- Precision Wire Funnels Eliminate Stray Strands

Application

Quick Connect/Disconnect Signal and Control

Specifications

Industry Standard(s)	• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07 • UL 2238 and UL50E, File No. E192071
EU RoHS Indicator	No

Conductor

Cable Specification	UL Listed Portable Cord
Cable Size	.24"-.32"

Current

Amperage Rating	12 A
Voltage Rating	250V kV

Dimensions



Thread Size

Non-Threaded

General

Material - O-Ring
Material - Overmold
OEM Brand Name
Specifications

Neoprene
PBT
Hubbell Wiring Device-Kellems

- Connector Insert - PUR/PA
- Connector Shell - PBT
- Contacts - Brass, gold plate over palladium nickel
- Coupling Nut - Anodized aluminum, SST consult factory

PUR/PA
783585192024
Aluminum
PBT

Logistics

Carton Quantity	30 EA
-----------------	-------

Operational

Operating Temperature	-40 Deg C to 85 Deg C
-----------------------	-----------------------

Product Assets

[Catalog \[English\]](#)