

Signal and Control Products, Mini-Quick, Male Extension Plug, 3-Pole, Field Attachable, F9

By Hubbell Wiring Device-Kellems
Catalog # [HIMS03F9](#)

Signal and Control Mini-Quick Male Extension Plug, 3-Pole, Field Attachable, F9



Features

- Superior Contact Design
- Body with High Impact Design
- Precision Wire Funnels Eliminate Stray Strands

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator	No
Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07• UL 2238 and UL50E, File No. E192071

Conductor

Cable Specification	UL Listed Portable Cord
Cable Size	.24"-.32"

Current

Amperage Rating	12 A
Voltage Rating	250V kV

Dimensions

Thread Size

Non-Threaded

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Material - Insert	PUR/PA
Material - Coupling Nut	Aluminum
Material - O-Ring	Neoprene
Material - Overmold	PBT
Specifications	<ul style="list-style-type: none">• Connector Insert - PUR/PA• Connector Shell - PBT• Contacts - Brass, gold plate over palladium nickel• Coupling Nut - Anodized aluminum, SST consult factory

UPC

783585192031

Material - Shell

PBT

Logistics

Carton Quantity	30
-----------------	----

Operational

Operating Temperature	-40 Deg C to 85 Deg C
-----------------------	-----------------------

Product Assets

[Catalog \[English\]](#)