

Signal and Control Products, Mini-Quick, Male Extension Plug, 5-Pole, Field Attachable, F13.5

By Hubbell Wiring Device-Kellems
Catalog # [HIMS05F13](#)

Signal and Control Products, Mini-Quick, Male Extension Plug, 5-Pole, Field Attachable, F13.5



Features

- Superior Contact Design
- Body with High Impact Design
- Precision Wire Funnels Eliminate Stray Strands

Application

Quick Connect/Disconnect Signal and Control

Specifications

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07• UL 2238 and UL50E, File No. E192071
----------------------	--

EU RoHS Indicator No

Conductor

Cable Specification UL Listed Portable Cord
Cable Size .39"-.47"

Current

Amperage Rating 9 A
Voltage Rating 250V kV

Dimensions

Thread Size

Non-Threaded

General

Material - O-Ring
Material - Overmold
OEM Brand Name
Specifications

Neoprene
PBT
Hubbell Wiring Device-Kellems

- Connector Insert - PUR/PA
- Connector Shell - PBT
- Contacts - Brass, gold plate over palladium nickel
- Coupling Nut - Anodized aluminum, SST consult factory

Material - Insert
UPC
Material - Coupling Nut
Material - Shell

PUR/PA
783585192260
Aluminum
PBT

Logistics

Carton Quantity 30

Operational

Operating Temperature -40 Deg C to 85 Deg C

Product Assets

[Catalog \[English\]](#)