

## Signal and Control, Mini Quick, Male Plug, Field Attachable, 3-Pole, .39"-.47" Cable Range

By Hubbell Wiring Device-Kellems  
Catalog # [HPMS03F13](#)

Signal and Control, Mini Quick, Male Plug, Field Attachable, 3-Pole, .39"-.47" Cable Range



### Features

- Superior Contact Design
- Body with High Impact Design
- Precision Wire Funnels Eliminate Stray Strands

### Application

Quick Connect/Disconnect Signal and Control

### Specifications

EU RoHS Indicator	No
Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07</li><li>• UL 2238 and UL50E, File No. E192071</li></ul>

### Conductor

Cable Specification	UL Listed Portable Cord
Cable Size	.39"-.47"

### Current

Amperage Rating	12 A
Voltage Rating	250V kV

### Dimensions

Thread Size

Non-Threaded

### General

OEM Brand Name	Hubbell Wiring Device-Kellems
Material - Insert	PUR/PA
Material - Coupling Nut	Aluminum
Material - O-Ring	Neoprene
Material - Overmold	PBT
Specifications	<ul style="list-style-type: none"><li>• Connector Insert - PUR/PA</li><li>• Connector Shell - PBT</li><li>• Contacts - Brass, gold plate over palladium nickel</li><li>• Coupling Nut - Anodized aluminum, SST consult factory</li></ul>

UPC

783585192079

Material - Shell

PBT

### Logistics

Carton Quantity	30
-----------------	----

### Operational

Operating Temperature	-40 Deg C to 85 Deg C
-----------------------	-----------------------

### Product Assets

[Catalog \[English\]](#)