

Signal and Control, Mini Quick, Male Plug, Field Attachable, 4-Pole, .39"-.47" Cable Range

By Hubbell Wiring Device-Kellems
Catalog # [HPMS04F13](#)

Signal and Control, Mini Quick, Male Plug, Field Attachable, 4-Pole, .39"-.47" Cable Range

Features

- Superior Contact Design
- Body with High Impact Design
- Precision Wire Funnels Eliminate Stray Strands

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator	No
Industry Standard(s)	• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07 • UL 2238 and UL50E, File No. E192071

Conductor

Cable Specification	UL Listed Portable Cord
Cable Size	.39"-.47"

Current

Amperage Rating	9 A
Voltage Rating	250V kV

Dimensions



Thread Size	Non-Threaded
-------------	--------------

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Material - Insert	PUR/PA
Material - Coupling Nut	Aluminum
Material - O-Ring	Neoprene
Material - Overmold	PBT
Specifications	• Connector Insert - PUR/PA • Connector Shell - PBT • Contacts - Brass, gold plate over palladium nickel • Coupling Nut - Anodized aluminum, SST consult factory

UPC	783585192185
Material - Shell	PBT

Logistics

Carton Quantity	30
-----------------	----

Operational

Operating Temperature	-40 Deg C to 85 Deg C
-----------------------	-----------------------

Product Assets

[Catalog \[English\]](#)