

## Signal and Control, Mini Quick, Male Plug, Field Attachable, 4-Pole, .47"-.55" Cable Range

By Hubbell Wiring Device-Kellems  
Catalog # [HPMS04F16](#)

Signal and Control, Mini Quick, Male Plug, Field Attachable, 4-Pole, .47"-.55" Cable Range



### Features

- Superior Contact Design
- Body with High Impact Design
- Precision Wire Funnels Eliminate Stray Strands

### Application

Quick Connect/Disconnect Signal and Control

### Specifications

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07</li><li>• UL 2238 and UL50E, File No. E192071</li></ul>
----------------------	--

EU RoHS Indicator No

### Conductor

Cable Specification	UL Listed Portable Cord
Cable Size	.47"-.55"

### Current

Amperage Rating	9 A
Voltage Rating	250V kV

### Dimensions

Thread Size

Non-Threaded

### General

Material - O-Ring  
Material - Overmold  
OEM Brand Name  
Specifications

Neoprene  
PBT  
Hubbell Wiring Device-Kellems

- Connector Insert - PUR/PA
- Connector Shell - PBT
- Contacts - Brass, gold plate over palladium nickel
- Coupling Nut - Anodized aluminum, SST consult factory

Material - Insert  
UPC  
Material - Coupling Nut  
Material - Shell

PUR/PA  
783585192192  
Aluminum  
PBT

### Logistics

Carton Quantity 30

### Operational

Operating Temperature -40 Deg C to 85 Deg C

### Product Assets

[Catalog \[English\]](#)