

## Straight Blade Receptacles, Decorator Duplex, Commercial, Corrosion Resistant, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R, Back and Side Wired, White

By Hubbell Wiring Device-Kellems  
Catalog # [IG15DRW](#)

Straight Blade Devices, Receptacles, Decorator Duplex, Commercial Grade, Corrosion Resistant, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R, Back and Side Wired, White



### Features

- Triangle marking on face indicates isolated ground
- Aesthetic Style Line® decorator design
- Triple wipe contacts

### Application

Heavy Duty

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R

### Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

### Current

Current Rating	15 A
Amperage Rating	15 A
Phase	Single Phase

Current / Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Wattage	1875
Voltage Rating	125 VAC

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	White
Item Type	Isolated Ground
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
UPC	783585146867

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[Spanish, French, English\]](#)