

Plates, INFINI Module, Stereo Jack, 110 Block, Electric Ivory

By Hubbell Wiring Device-Kellems
Catalog # [IMAR1101EI](#)

Plates, INFINI Module, Stereo Jack, 110 Block, Electric Ivory



Features

- INFINI Module
- Stereo Jack
- 110 Block
- Electric Ivory

Application

2 RCA Left Right Audio

Specifications

EU RoHS Indicator Yes

Current

Connectivity 110 Punch Down
Withstand Voltage 1000V RMS, 1414V DC
Contact Resistance 100 Ohm

General

Material - Mounting Hardware Type
Specifications

Snap-On- Snap-Fit
RCA

- AV Module - RCA
 - AV Module Type - RCA Composite Video with Audio to 110 Termination
 - Unit Package - Single
- 662620858333
Left/Right Audio

UPC
Style

Logistics

Carton Quantity 25

Operational

Temperature Rating Per TIA

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)