

Signal and Control, Micro-Quick, Female Plug, 3-Pole, LED Cable, 15M Length

By Hubbell Wiring Device-Kellems
Catalog # [MCMPS13115](#)

Signal and Control, Micro-Quick, Female Plug, 3-Pole, LED Cable, 15M Length



Features

- Micro-Quick3-Pole
- LED Cable

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Number Of Conductors 3-Pole

Dimensions

Diameter Live Part .67"

Length 590.551 in

General

Jacket PVC
OEM Brand Name Hubbell Wiring Device-Kellems
UPC 783585524504
Color Black

Logistics

Carton Quantity 10

Operational

Temperature Rating -20 Deg C to 105 Deg C

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)