

MCMS14110

By Hubbell Wiring Device-Kellems
Catalog # [MCMS14110](#)

Micro-Quick, Female Plug, 4P, Single Key, #22AWG



Application

Quick Connect/Disconnect Signal and Control

General

Catalog Number	MCMS14110
Color	Black
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Female Straight Plug
Jacket	PVC
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585228464

Dimensions

Diameter Live Part	.59"
Length	393.701 in

Conductor Related

Conductor Type	Copper
Number of Conductors	4-Pole

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD1527_INSTALLINST](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_MCMS14_DRAWING_PDF](#)
[Specifications - MCMS14110 Specification Sheet French](#)
[Specifications - MCMS14110 Specification Sheet English](#)