

Signal and Control, Micro Quick, Female Plug, Field Attachable, 4-Pole, .24-.35" Cable Range

By Hubbell Wiring Device-Kellems
Catalog # [MCMS14F9](#)

Signal and Control, Micro Quick, Female Plug, Field Attachable, 4-Pole, .24-.35" Cable Range



Features

- Body with high impact design
- Strain relief protects terminations
- Precision wire funnels eliminate stray strands

Application

Quick Connect/Disconnect Signal and Control

Specifications

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07• UL 2238 and UL50E, File No. E192071
EU RoHS Indicator	No

Conductor

Cable Specification	UL Listed Portable Cord
Cable Size	.24"-.32"

Current

Amperage Rating	4 A
Voltage Rating	250V kV

Dimensions

Thread Size

Non-Threaded

General

Material - O-Ring
Material - Overmold
OEM Brand Name
Specifications

Neoprene
PBT
Hubbell Wiring Device-Kellems

- Connector Insert - Nylon
- Connector Shell - PBT
- Contacts - Brass, gold plate over palladium nickel
- Coupling Nut - Nickel plated brass, SST consult factory

Material - Insert
UPC
Material - Coupling Nut
Material - Shell

PUR/PA
783585192420
Aluminum
PBT

Logistics

Carton Quantity 30

Operational

Operating Temperature -40 Deg C to 85 Deg C

Product Assets

[Catalog \[English\]](#)