

Signal and Control, Micro Quick, Female Plug, Field Attachable, 5-Pole, .16-.24" Cable Range

By Hubbell Wiring Device-Kellems
Catalog # [MCMS15F7](#)

Signal and Control, Micro Quick, Female Plug, Field Attachable,
5-Pole, .16-.24" Cable Range



Features

- Body with high impact design
- Strain relief protects terminations
- Precision wire funnels eliminate stray strands

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator	No
Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07• UL 2238 and UL50E, File No. E192071

Conductor

Cable Specification	UL Listed Portable Cord
Cable Size	.16"-.24"

Current

Amperage Rating	4 A
Voltage Rating	250V kV

Dimensions

Thread Size

Non-Threaded

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Material - Insert	PUR/PA
Material - Coupling Nut	Aluminum
Material - O-Ring	Neoprene
Material - Overmold	PBT
Specifications	<ul style="list-style-type: none">• Connector Insert - Nylon• Connector Shell - PBT• Contacts - Brass, gold plate over palladium nickel• Coupling Nut - Nickel plated brass, SST consult factory

UPC

783585192499

Material - Shell

PBT

Logistics

Carton Quantity	30
-----------------	----

Operational

Operating Temperature	-40 Deg C to 85 Deg C
-----------------------	-----------------------

Product Assets

[Catalog \[English\]](#)