

LINKOSITY® Feed - UL Type 4X Rated**

4X Rated NEMA Standard Items

Description	Catalog Number
20A 125V Straight Blade†	MLWF2010
20A 125V WTSSTL	MLWF2020
20A 125V Straight Blade, Pass-Thru	MLWF201P
20A 125V WTSSTL, Pass-Thru	MLWF202P
20A 125/250V WTSSTL, No Pass-Thru	MLWF2070
30A 125V WTSSTL, No Pass-Thru	MLWF1050
30A 250V WTSSTL, No Pass-Thru	MLWF1060
30A 125V WTSSTL, No Pass-Thru	MLWF2050
30A 250V WTSSTL, No Pass-Thru	MLWF2060

All LINKOSITY® - UL Type 4X Rated*

4X Rated LINKOSITY Standard Items

Description	Catalog Number
20A 3W up to 600V, 4 Port	M4L2003PB0
20A 3W up to 600V, 4 Port Pass-Thru	M4L2003PBP

Conduit Feed - UL Type 4X Rated**

Conduit Feed Standard Items

Description	Catalog Number
20A 125V Straight Blade	MCWF2010
20A 125V WTSSTL	MCWF2020
20A 250V WTSSTL	MCWF2030
20A 277V WTSSTL	MCWF2040
30A 125V WTSSTL	MCWF2050
30A 250V WTSSTL	MCWF2060
20A 125/250V WTSSTL	MCWF2070
20A 3Ø, 250V WTSSTL	MCWF2080
20A 3Ø, 480V WTSSTL	MCWF2090
30A 125/250V WTSSTL	MCWF2100
30A 3Ø 250V WTSSTL	MCWF2110
30A 3Ø 480V WTSSTL	MCWF2120
30A 3Ø 600V WTSSTL	MCWF2130

Note: **Watertight Safety-Shroud® Twist-Lock® Plug required when in use.

†Straight Blade are UL Type 4X when not in use only.

•Closure cap required when not in use.

Accepts PH2304 series cables.

WTSSTL is an abbreviation for Watertight Safety-Shroud® Twist-Lock®.



Device Type	Style	Type	No. of Devices	Device Type	Pass-Thru
M	L - LINKOSITY	WF - Watertight Safety-Shroud Receptacle	1	01 - 20A 125V Straight Blade†	P - Pass-Thru 0 - No Pass-Thru
			2	02 - 20A 125V Twist-Lock 03 - 20A 250V Twist-Lock 04 - 20A 277V Twist-Lock 05 - 30A 125V Twist-Lock 06 - 30A 250V Twist-Lock 07 - 20A 125/250V Twist-Lock 08 - 20A 3Ø 250V Twist-Lock 09 - 20A 3Ø 480V Twist-Lock 10 - 30A 125/250V Twist-Lock 11 - 30A 3Ø 250V Twist-Lock 12 - 30A 3Ø 480V Twist-Lock 13 - 30A 3Ø 600V Twist-Lock	
		WM - Watertight Safety-Shroud Inlet			



Device Type	Style	Type	No. of Poles	Conductor Colors	Pass - Thru
M	4L - LINKOSITY	20 - 20A	02	PA - Green/Yellow Black (all others)	P - Pass-Thru 0 - No Pass-Thru
		23 - 20A Super Neutral Isolated Ground	03		
			04	PB - Green/Yellow White Black (all others)	
		30 - 30A	05 06		



Device Type	Style	Type	No. of Devices	NEMA Device Type	Pass-Thru
M	C - Conduit Feed	WF - Watertight Safety-Shroud Receptacles	2	01 - 20A 125V Straight Blade	0 - No Pass-Thru
				02 - 20A 125V Twist-Lock	
				03 - 20A 250V Twist-Lock	
				04 - 20A 277V Twist-Lock	
				05 - 30A 125V Twist-Lock	
				06 - 30A 250V Twist-Lock	
				07 - 20A 125/250V Twist-Lock	
				08 - 20A 3Ø 250V Twist-Lock	
				09 - 20A 3Ø 480V Twist-Lock	
				10 - 30A 125/250V Twist-Lock	
				11 - 30A 3Ø 250V Twist-Lock	
				12 - 30A 3Ø 480V Twist-Lock	
				13 - 30A 3Ø 600V Twist-Lock	
				WM - Watertight Safety-Shroud Inlet	



Replacement Mounting Feet

Description Catalog Number

For Power Distribution Assemblies.

HBLRFT1^Δ

Note: ^Δ Package of 10 mounting feet and 10 screws.