

Micro-Quick Control Connectors, Male Angled, 3 Wire, Insulation Displacement

By Hubbell Wiring Device-Kellems
Catalog # [MIMA13IDC](#)

Micro-Quick Control Connectors, Male Angled, 3 Wire, Insulation Displacement

Features

- Strain relief bushing protects terminations
- Wire Guide for virtually toolless termination
- Insulation displacement contacts are made of Copper Alloy

Application

Quick Connect/Disconnect Signal and Control

Specifications

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07• UL 2238 and UL50E, File No. E192071
EU RoHS Indicator	Yes
Conductor	
Conductor Type	Copper
Number Of Conductors	3-Pole
Dimensions	
Diameter Live Part	.67"



General

OEM Brand Name	Hubbell Wiring Device-Kellems
Specifications	<ul style="list-style-type: none">• Contact Materials - Copper Alloy• Contact Plating - Tin over Nickel• Housing - Polyester Elastomer, Black• Strain Relief Bushing - Neoprene, Black• Wire Guide - Nylon 6/6, Gray
UPC	783585226705
Color	Black

Logistics

Carton Quantity	25
-----------------	----

Operational

Temperature Rating	-20 Deg C to 105 Deg C
--------------------	------------------------

Product Assets

[Catalog \[English\]](#)