

Signal and Control, Micro Quick, MalePlug, Field Attachable, 4-Pole, .16-.24" Cable Range

By Hubbell Wiring Device-Kellems
Catalog # [MIMS14F9](#)

Signal and Control, Micro Quick, MalePlug, Field Attachable, 4-Pole, .16-.24" Cable Range

Features

- Body with high impact design
- Strain relief protects terminations
- Precision wire funnels eliminate stray strands

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator	No
Industry Standard(s)	• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07 • UL 2238 and UL50E, File No. E192071

Conductor

Cable Specification	UL Listed Portable Cord
Cable Size	.24"-.32"

Current

Amperage Rating	4 A
Voltage Rating	250V kV

Dimensions



Thread Size	Non-Threaded
General	
OEM Brand Name	Hubbell Wiring Device-Kellems
Material - Insert	PUR/PA
Material - Coupling Nut	Aluminum
Material - O-Ring	Neoprene
Material - Overmold	PBT
Specifications	• Connector Insert - Nylon • Connector Shell - PBT • Contacts - Brass, gold plate over palladium nickel • Coupling Nut - Nickel plated brass, SST consult factory
UPC	783585192468
Material - Shell	PBT
Logistics	
Carton Quantity	30
Operational	
Operating Temperature	-40 Deg C to 85 Deg C
Product Assets	
Catalog [English]	