

Signal and Control, Linkosity, Power System Distribution Assembly, 3-Gang, Spec Grade, with Pass Thru

By Hubbell Wiring Device-Kellems
Catalog # [MSL3SG00P](#)

Signal and Control, Linkosity, Power System Distribution Assembly, 3-Gang, Spec Grade, with Pass Thru



Features

- Linkosity
- Power System Distribution Assembly
- 3-Gang
- Spec Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	Non-NEMA

Conductor

Number Of Wires	4-Wire Grounding
Wire Size	#12 AWG
Number Of Poles	3-Pole

Current

Phase	Single Phase Control
Current / Amperage Rating	20 A

Connectivity	Plug Together
Current Rating	20 A
Amperage Rating	20 A
Wattage	5000
Voltage Rating	250V AC Max kV

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

Item Type	Conduit Feed Pre-Wired Box
Material - Mounting Hardware	Screw Mounting
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Thermoplastic
UPC	783585521695
Color	Gray

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)